

Interlinings in a crusher

Abrasive

✓ Pressure of crushing plate

Function

✓ Interlinings

Processing

✓ Plasmacutting
✓ Loose cassette mounting

Comparative tests



LedinsGrusAB
ledinsgrus.se 0570-32044 Gunnarskog

Compared solutions	Replacement/turning of the crushing plate
450HB plate, thickness 8 mm	2 times
CREUSABRO® 8000® plate, thickness 6 mm	minimum 4 times

CREUSABRO® 8000®
minimum +100%

BERGS
MEKANISKA